NORTH CAROLINA DEPARTMENT OF HEALTH AND HUMAN SERVICES DIVISION OF PUBLIC HEALTH ENVIRONMENTAL HEALTH SECTION ON-SITE WATER PROTECTION BRANCH

SEPTIC TANK EFFLUENT FILTER APPROVAL

Septic Tank Effluent Filter Approval Number: EF-12-R6

Issued To: Polylok, Inc

3 Fairfield Blvd

Wallingford, CT 06492 www.polylok.com

Contact: Patrick Mulhall

203-284-8514

For: Septic Tank Effluent Filter Model PL-122 with Pipe Adapter, Model PL-68, Model PL-250, Model PL-

525, and Model PL-625

Date: December 18, 1998

February 2, 2004 Addition of Model PL-68
March 4, 2005 Addition of Model PL-525
December 21, 2005 Addition of Model PL-625
October 1, 2015 Addition of Model PL-250

December 31, 2024 Updated for 18E and renewed for 2025

In accordance with G.S. 130A-335 and 130A-335.1 and 15A NCAC 18E .1404 and .1405, an application by Polylok, Inc, for renewal of their approval for septic tank effluent filters has been reviewed and approved when the following conditions are met.

I. Description

- a. Effluent filters shall be designed and manufactured in accordance with the plans, specifications and documents submitted by the manufacturer with the application.
- b. Effluent filters shall meet the specifications in Table I.

| Table I. Approved Filter Model Specifications | | | | | | |
|--|---|--|-----------------------|------------------------------------|--------------------------|---|
| Filter Models | Size | Support Case ¹ | Case Dimensions | | Min. Tank | Min. Access |
| | | | Above Liquid Level | Below Liquid Level ² | Liquid Depth Required | Opening Size ³ |
| PL-122 With Pipe Adapter ¹ | 4.5 inches square x 22.75 inches (18 inches to case inlet) | 4.5 inch square housing | 5.75 | 12.375 | 36 | 15 x 15, 17 inch diameter, or equal |
| Dual PL-122 With Pipe Adapter ^{1,2} | 2 filters, each 4.5 inches square x 22.75 inches (18 inches to case inlet) | 2 attached cases, 4.5 inch square housings | 5.75 | 12.375 | 36 | 17 x 17, 17 inch diameter, or equal |

| Triple PL-122 With Pipe Adapter ^{1,2} | 3 filters, each 4.5 inches square x 22.75 inches (18 inches to case inlet) | 3 attached cases, 4.5 inch square housings | 5.75 | 12.375 | 36 | 18 x 18, 20 inch diameter, or equal |
|--|--|--|--|--|----|---|
| PL-68 | 2-5/8 inch diameter x 14 inches | 4 inch PVC Tee | 6 | 15.5 | 36 | 15 x 15, 17 inch diameter, or equal |
| PL-525 | 9.5 inches x 11inches x 22 inches | 11.5 inch x 10.5 inch housing | 8.5 (6 in Sch 40) 7.5 (4 in Sch 40) | 24.5 (6 in Sch 40) 25.5 (4 in Sch 40) | 36 | 17 x 17, 17 inch diameter, or equal |
| PL-625 | 9.5 inches x 11inches x 22 inches | 11.5 inch x 10.5 inch housing | 8.5 (6 in Sch 40) 7.5 (4 in Sch 40) | 24.5 (6 in Sch 40) 25.5 (4 in Sch 40) | 36 | 17 x 17, 17 inch diameter, or equal |
| PL-250 | 6 inch diameter x 15.75 inches | 6 inch ABS Tee | 6 | 16 | 36 | 17 x 17, 17 inch diameter, or equal |

Notes:

- 1. Solvent weld filter support case to 3-inch or 4-inch PVC Schedule 40 outlet pipe.
- 2. Dual and Triple models require cases to be snapped together in accordance with filter manufacturer's specifications.
- 3. Support case housings are integral to all PL-122 and 525 filters and supplied by Polylok, Inc. for all models. Supplemental support may be provided by the septic tank manufacturer, by inserting a 4-inch thin-wall PVC pipe into the housing of the furthest filter from the outlet after the shut off ball has been removed in accordance with manufacturer's specifications, fastening this pipe with two stainless steel screws to the housing, and extending the support pipe to the tank bottom. Supplemental support is required for Model PL-525. Openings in the support pipe must be located to meet the 25% to 40% requirement for the support case inlet intake. Support case for Model PL-68 provided by Polylok, Inc. or septic tank manufacturer.
- 4. When the tank liquid depth exceeds 50 inches, the case bottom must be extended as necessary to meet the 25% to 40% inlet intake requirement for the filter support case. This may be accomplished by removing the shut off ball, in accordance with filter manufacturer's specifications, and fastening with two stainless steel screws to the housing a 4-inch thin wall PVC pipe cut to the length needed to meet this requirement.
- 5. Other minimum opening sizes or configurations proposed by the septic tank manufacturer shall be approved by the State of a case-by-case basis if documentation is provided showing both adequate access is provided for filter maintenance and for pumping the tank outlet compartment.

II. Sizing

The approved effluent filters may be used in approved septic tanks. The approved flow capacities are shown in Table II. The effluent filter sizing must be compatible with the design daily flow and the minimum septic tank size in accordance with 15A NCAC 18E .0801.

| Table II. Effluent Filter Sizing Criteria ^{1,2} | | | | |
|--|-----------------------------------|--|--|--|
| Filter Model | Maximum Design Flow (gallons/day) | | | |
| | | | | |
| PL-122 With Pipe Adapter | 800 | | | |
| Dual PL-122 With Pipe Adapter | 1,600 | | | |
| Triple PL-122 With Pipe Adapter | 2,400 | | | |
| PL-68 | 800 | | | |
| PL-525 | 3,000 | | | |
| PL-625 | 3,000 | | | |
| PL-250 | 3,000 | | | |

Notes:

EF-12-R6 December 31, 2024 Page 3 of 3

- 1. Sizing based on domestic strength effluent in accordance with 15A NCAC 18E .0402(a), Table III.
- 2. If the effluent filters are used in a system with a design daily flow greater than 3,000 gallons/day, the design requires a Professional Engineer and a project specific approval.

III. Installation

The effluent filters and effluent filter support case shall be assembled and installed in accordance with the filter manufacturer's specifications and applicable rules. The filter case shall be located in such a manner that the filter can be readily accessible by the operator from the access opening and removable by hand from finished grade. The access opening shall also provide enough room to allow for pumping of the tank compartment. An access device manufactured by Polylok, Inc, shall be provided whenever the tank is installed with the filter handle deeper than 18-inches below the access opening or more than 18-inches below finished grade.

IV. Operation and maintenance

Effluent filters shall be used and maintained in accordance with the effluent filter manufacturer's specifications and applicable laws and rules. Manufacturer-specified procedures shall be followed to minimize the bypass of unfiltered effluent while the filter is being removed when servicing is needed. Polylok, Inc, has available for purchase a slotted sleeve removal tool that prevents material from leaving the outlet tee while the filter is being replaced. Upon removal, effluent filters shall either be replaced with a new effluent filter and the used effluent filter disposed of in an approved disposal method, or debris shall be washed off the effluent filter into the septic tank and the effluent filter placed back into service.

| Approved by: | Date: |
|--------------|-------|